

## System Configuration & Specification

|            |                                            |                                                       |
|------------|--------------------------------------------|-------------------------------------------------------|
| Tube Stand | Height of the Tube Stand                   | 93 Inches                                             |
|            | Vertical Travel                            | Max =62 Inches - Min = 12 Inches                      |
|            | Lowest Point                               | 9 Inches from Floor to Tube Center                    |
|            | Transverse Travel                          | (+/-)13.5 Inches ( MX 30+ Only )                      |
|            | Tube Rotation                              | (+/-)135                                              |
|            | Control Screen for Tube Rotation SID Angle | Analog with Push Button Control and One Touch Release |
|            | Vertical Travel Control                    | Electromagnetic Brakes - 24 VDC, 2 Amp                |

|             |                            |                                   |
|-------------|----------------------------|-----------------------------------|
| Chest Stand | Height of the Chest Stand  | 89 Inches                         |
|             | Vertical Travel            | Max : 73 Inches - Min : 12 Inches |
|             | Bucky Tray Accommodates    | 14" x 17" / 17" x 17"             |
|             | Grid and Ion Chamber Ready | Easy Install                      |
|             | Universal Bucky Tray       | Left-Handed Default               |
|             | Patient Hand Rail          | Can be Left or Right              |

|             |                            |                                            |
|-------------|----------------------------|--------------------------------------------|
| Floor Mount | Standard 5' Floor Mount    | Longitudinal Travel Focal Spot : 32 Inches |
|             | Optional 2' Extension      | Increase Travel                            |
|             | Pass - Through Cable Slots | For Better Cable Management                |
|             | Travel Control             | Electromagnetic Brakes - 24 VDC, 2 Amp     |

\* All specifications can change without prior notice.

