

# Leica, the standard for individual solutions

## Leica Photoautomats & Digital Cameras


### Eyepieces

10 447 160  
10 445 301  
10 445 302  
10 445 303

### Tubes



10 445 619 45°



10 445 822 10-50°




10 445 924  
10 446 229

### Video/Photo

### ErgoModule™




10 446 123 5°-25°



10 446 171 30-120mm




10 446 180



10 479 887  
Discussion

10 446 093 / 10 446 143  
10 446 144 / 10 446 145  
10 446 146 / 10 446 147  
10 446 159 / 10 446 234  
**Fluorescence module**

### Optics Carriers



10 446 272 MZ9s

### Objectives



10 411 589 1x  
10 422 562 1.5x  
10 422 561 2x  
10 473 832 0.8x  
10 445 201 0.63x  
10 422 563 0.5x  
10 422 564 0.32x  
**Achromatic**




10 446 275 1x Plan  
10 446 157 0.5x Plan  
10 447 075 0.8x Plan  
10 447 157 1x Planapo  
10 447 050 1.6x Planapo  
10 446 236 0.63x Planapo  
10 447 101 2x Planapo  
**Plan/Planapo**




10 447 148  
**Ergo 0.4-0.63x**


### Microscope Carriers




10 445 617



10 445 618




10 446 176 / 10 447 041  
**Motorfocus**



10 446 259


**Motorfocus for swing-arm**

### Focusing drive with column




10 447 106 / 10 447 185  
**Coarse / Fine**

### Stands




10 445 367  
**HL Transmitted-light**



10 445 387 **BF**  
10 445 363 **BF / DF**



10 368 078  
**Polarization**



10 445 631  
**Incident-light**