


E-750.CP

High-Speed Digital NanoAutomation® Controller



E-750.CP controller with
P-752 NanoPositioning stage

Application Examples

- Head / media test
- Track profiling
- Scanning-probe microscopy
- Micro-ablation and active optics.

Ordering Information

E-750.CP
Digital NanoAutomation® Controller

E-751.PCI
PCI Card with FiberLink Interface for
three E-750

E-751.PIO
Parallel-Port-to-Fiber Converter

Options

E-751.F05
5 m FiberLink Cable

**Custom Designs
for Volume Buyers**

Notes

Important Calibration Information:
Please read details on page 6-41.

- **Ultra-Fast Servo Loop:**
90 μ sec
- **Optical FiberLink Interface (Optional):** 1 Mbit/s
- **DSP-Based Real-Time Operating System**
- **Additional High-Speed Analog Input**
- **Optional InputShaping™**
- **AutoCalibration Function for NanoPositioning Systems with ID Chip**
- **All Servo-Parameters Stored in Flash ROM**

The new E-750.CP digital PZT controller offers unmatched responsiveness and precision for the most demanding OEM applications. Driving the ultra-fast P-752 and P-753 series NanoStages, the E-750 provides sub-millisecond settling and sub-angstrom (0.1 nm) resolution.

Optional InputShaping™

The E-750 complements ultra-low-noise PZT power amplifier, capacitive position sensing circuitry and sophisticated digital signal processing with fast servo-control algorithms. It is also the first system on the market offering PI's exclusive Mach™ Throughput Coprocessor technology (InputShaping™), which achieves the fastest possible overall system throughput by eliminating the effect of mechanical resonances (optional).


AutoCalibration

OEM customers will appreciate the AutoCalibration function, allowing random combination (and easy interchange) of controllers and NanoPositioning systems with factory default configuration. Calibration data, linearization data and optimized servo-control parameters are stored in each NanoPositioning system and read by the controller upon power-up.

Digital Linearization

A digital linearization algorithm and the exclusive use of precision components in the controller guarantee excellent linearity and position accuracy.

The controller is equipped with a wide-range power supply for use throughout the world.



E-750.PIO parallel-port-to-fiber converter allows operation of the E-750 from a 24-bit, high-speed parallel-port interface

PZT Actuators

PZT Flexure NanoPositioners

PZT Active Optics / Steering Mirrors

Tutorial: Piezoelectrics...

Capacitive Position Sensors

PZT Control Electronics

MicroPositioners / Hexapod Systems


Photonics Alignment & Packaging Systems

Motor Controllers


Index

<http://www.pi.ws>

info@pi.ws



E-751.PCI, PCI card with FiberLink
interface for operation of up to 3 E-750 controllers



E-750 software tool allows step-and-settle analysis and optimization of connected NanoPositioning system.

Technical Data

Models

E-750.CP
Digital NanoAutomation® Controller

Function

Digital NanoAutomation® Controller

Channels

1

Processor

32-bit floating point DSP, 50 MHz

Sampling rates

30 µs (Sensor), 90 µs (Servo Loop)

Effective resolution DAC

20 bits

Sensor types

Capacitive, two-plate sensors

RS-232 interface

115 kBit/s, BiSync protocol, ISO 1745-1975 (E)

Fiber-Link interface (optional)

1 MBit/s

Max. output power

10 W (see page 6-40)

Current limitation

Short-circuit proof

Output voltage range

-20 to +120 V

PZT and sensor connector

Combo sub-D; size DB, layout 7W2, 137W2SC30N40x (CONEC)

Dimensions

125 x 50 x 262 mm

Weight

2 kg

Operating voltage range

90-264 VAC, 50-60 Hz, 30 VA